

Technical Data Sheet

General

Article number: 2061
Description: Masking Film Dispenser Smart



Specification:

Easy to use masking film dispenser. Use the carton box of the Colad Masking Film on the Masking Film Dispenser Smart to prevent dust contamination.

Features and benefits

- Less dust contamination: Less dust on the masking film due to the closed carton box (with dispenser function).
- Dispenser can be stored vertically for space-saving
- Mobile, easy to move
- Easy to operate by 1 person.
- Use carton box as cutting guide.

Suitability

Suitable for all Colad masking films in combination with the cardboard box with built-in dispenser function. Also for other brands with a square cardboard box and dispenser function. Maximal size of box of 110 cm long, 24 cm wide and 24 cm high.



Technical Specification:

Color	Red
Material	Metal
Packaging unit	1 piece
Packing Box size (l x w x h)	
Product size (l x w x h)	120 x 54 x 44 cm (outer dimension)
Weight	8.5 kg
Maximal film box size (l x w x h)	110 x 24 x 24 cm (A dispenser functionality is required.)

*vertical
storage
position*


USER MANUAL

First time use: Mount a box with foil (horizontal application):

1. Loosen the black knobs from the 'top part'. The top has a handle and is attached to the central rod:



2. Slide the entire top slightly outwards so that there appears space in the length for the box.




3. Loosen the black knobs at the bottom, at the wheels. Slide the 'red holders' out as far as possible. Tighten the black knobs so that the 'red holders' remain upright.



4. Place the box from the side of the dispenser. Place it as close as possible to the bottom (at the wheels).



5. Slide the top (with the handle) against the box. Tighten the black knobs from the top to the central rod to fixate the top part.



+



6. Slide the all the 'red holders' against the box. Tighten the black knobs to fix the box.



Film replacement with a similar film dispenser box:

1. Loosen the black knobs at the bottom (at the wheels) and slide the 'red holders' out as far as possible.
2. Tighten the black knobs. This keeps the 'red holders' up.
3. Place the box with the foil from the side. Place it as close as possible to the bottom (at the wheels).
4. Slide the 'red holders' against the box. Tighten the black knobs to fixate the box.

Related products of Colad

Article number: 6365 – Transparent Masking Film 4 x 300 m

Article number: 2070 – Magnetic Foil Cutter

Disclaimer

Technical Data Sheet & Material Safety Data Sheet; it is the responsibility of the user to read understands and apply the information of the TDS. The information about work and environmental safety is available on the material safety data sheet (MSDS) via www.colad.co. It is the responsibility of the user to read and apply the information.

Products are for professional use. Necessary protective equipment and clothing should be worn.

The repairs should always be done in accordance with the OEM rules and specifications.

All information is for the user's consideration, investigation and verification. The specific use applications and conditions of use are beyond the control of EMM International B.V. It is the responsibility of the user to determine the suitability of any of the products mentioned for the user's specific application.

Created by:

EMM International BV

Bohemenstraat 19, 8028 SB Zwolle, The Netherlands

www.emm.com



T +31(0)38 467 66 00

www.colad.co